NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. CENTERING TOLERANCE (AT 532nm): BEAM DEVIATION: ±3 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


\$1, \$2, \$3 & \$4: R(abs) <0.25% @ 532nm \$5: Tp/Ts >1000:1 @ 532nm TRANSMISSION >95% REFLECTION >99.5%

4. FINE GROUND SURFACE

5. Elements to be cemented with norland optical adhesive 61

6. PROTECTIVE BEVEL AS NEEDED

7. MARK IDENTIFIES BEAMSPLITTER COATING RIGHT ANGLE PRISM



R

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	\$1, \$2, \$3, \$4	\$5				Edmund Optic	CS®
SHAPE	PLANO	PLANO	THIRD ANGLE		TITLE	50mm, 532nm, LASER LINE POLARIZING CUBE BEAMSPLITTER	
SURFACE FLATNESS	λ/4	λ/4					
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	90	90	ALL DIMS IN	mm	DWG NO	48862	SHEET 1 OF 1