


NOTES:

- 1. SUBSTRATE:
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1: ALUMINUM WITH PROTECTIVE OVERCOAT W/ BLACK OVERPAINT
R(AVG) > 85% FROM 400-700nm @ 0° AOI
R(AVG) > 90% FROM 400-2,000nm @ 0° AOI

S2: VIS 0°
R(AVG) ≤ 0.4% FROM 425-675nm @ 0° AOI


3. FINE GRIND SURFACE

- 4. RoHS COMPLIANT
- 5. TYPICAL ENERGY DENSITY: 0.3 J/cm² @ 10ns @ 532nm & 1064nm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div><div><div>THIRD ANGLE PROJECTION</div><div></div></div><div><div>GO[®] Edmund Optics[®]</div><div><div>TITLE</div><div>50mm, Aluminum & VIS 0° Coated, N-BK7 Right Angle Prism</div></div><div><div>ALL DIMS IN</div><div>mm</div><div>DWG NO</div><div>48557</div><div>SHEET 1 OF 1</div></div></div></div>			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	63.63 x 45	45 x 45				
COATING APERTURE	63.63 x 45	45 x 45				
SURFACE FLATNESS	λ/4	λ/4				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				