


NOTES:

1. SUBSTRATE:  
Fused Silica
2. S2 TO BE PARALLEL TO S1 TO WITHIN <3 ARCMINS
3. COATING (APPLY ACROSS COATING APERTURE)

S1 & S2: 515nm High Laser AR Coating  
R(ABS) < 0.10% @ 515nm @ 0° AOI

DAMAGE THRESHOLD,  
PUSLED: 10 J/cm<sup>2</sup> @ 20ns , 20 Hz @ 515nm


4. FINE GROUND SURFACE
5. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACE
6. ROHS COMPLIANT




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	10-5	10-5
SURFACE FLATNESS	0.10 WAVE	0.10 WAVE
CLEAR APERTURE	Ø22.86	Ø22.86
COATING APERTURE	Ø22.86	Ø22.86
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: 0.1R 515nm Laser Window 25.4 Dia x 6.35

DWG NO: 11254

SHEET 1 OF 1