




FOCAL LENGTH (EFL): 12 ±0,12
BACK FOCAL LENGTH (BFL): 9,26

1 AR COATING: UV-AR
R(ABS) ≤ 1,0% FROM 250-425nm @ 0° AOI
R(AVG) ≤ 0,75% FROM 250-425nm @ 0° AOI
R(AVG) ≤ 0,5% FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	5,502±0,006 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	8,1		Øe	8,1
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
SCALE: NONE
λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

9mm Dia, x 12mm FL UV-AR Coated,
UV Plano-Convex Lens

DWG NO

48673

SHEET SIZE
A4

SHEET
1 OF 1