


NOTES:

1. SUBSTRATE:
FLOAT GLASS
2. COATING
VACUUM DEPOSITED DURABLE CHROMIUM PATTERN
3. LINE PAIRS : 1-128
LINE WIDTH TOLERANCE (mm): $\pm 12.1-1.0 \mu\text{m}$
4. OPTICAL DENSITY: ≥ 3.0
5. CHANGES IN FREQUENCY STEPS:
1.1, 1.25, 1.4, 1.6, 1.8, 2.0, 2.2, 2.5, 2.8, 3.2, 3.6, 4.0,
4.5, 5.0, 5.6, 6.3, 7.1, 8.0, 9.0, 10.0, 11.0, 12.5, 14.0,
16.0, 18.0, 20.0, 23.0, 26.0, 29.0, 32.0, 40.0, 45.0, 51.0, 57.0, 64.0,
72.0, 80.0, 90.0, 101.0, 114, 128, 143, 161, 180
6. SURFACE QUALITY: 60-40




PLEASE NOTE:
NBS 1963A AREA ENLARGED

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO
CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR
REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	1-128, 101.6 x 101.6mm NBS 1963A Negative Target	
ALL DIMS IN	mm	DWG NO	85277	SHEET 1 OF 1