



FOCAL LENGTH (EFL):  $125 \pm 1,25$   
 BACK FOCAL LENGTH (BFL): 122,7

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$64,62 \pm 0,065$ CX	GLASS N-BK7 517/642	R	$\infty$ PL
$\text{Øe}$	24		$\text{Øe}$	24
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6$  nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 25,0mm Dia, x 125,0mm FL, Uncoated, Plano-Convex Lens

DWG NO 32861

SHEET SIZE A4  
 SHEET 1 OF 1