



FOCAL LENGTH (EFL): 400 ± 4
 BACK FOCAL LENGTH (BFL): 398,75

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	417,54±0,418 CX	GLASS N-K5 523/595	R	417,54±0,418 CX
Øe	24		Øe	24
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,91'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION	Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE $\lambda = 587,6$ nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	25mm Dia, x 400mm FL Uncoated, DCX N-K5 Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm	DWG NO	32904
INDICATIONS IN ACCORDANCE WITH ISO 10110					SHEET 1 OF 1