



FOCAL LENGTH (EFL): 50 ±0,5
 BACK FOCAL LENGTH (BFL): 46

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	22,923±0,023 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	24		Øe	24
3/	0,5 (0,1) λ=632,8 nm		3/	0,5 (0,1) λ=632,8 nm
4/	-		4/	2,18'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION				
ROHS: COMPLIANT	SCALE: NONE					λ = 587,6nm
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	25mm Dia, x 50mm FL Uncoated, M20 PCX Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	mm	DWG NO
INDICATIONS IN ACCORDANCE WITH ISO 10110				SHEET SIZE	A4	SHEET 1 OF 1