



FOCAL LENGTH (EFL): 200 ±2
 BACK FOCAL LENGTH (BFL): 198,02

1 AR COATING: 405nm V-COAT
 R(ABS) < 0,25% @ 405nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	91,692±0,092 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION						
ROHS: COMPLIANT	SCALE: NONE					λ = 587,6nm		
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE		25mm Dia, x 200mm FL 405nm V-Coat, UV PCX Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	mm	DWG NO	34077	SHEET SIZE
INDICATIONS IN ACCORDANCE WITH ISO 10110							SHEET	1 OF 1