



FOCAL LENGTH (EFL): 50 ± 0,5
 BACK FOCAL LENGTH (BFL): 46

1 AR COATING: 355nm Laser AR Coating
 R(ABS) < 0,25% @ 355nm @ 0° AOI
 DAMAGE THRESHOLD
 PULSED: 7,5J/cm² @ 20ns, 20Hz @ 355nm

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	22,923±0,023 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	24		Øe	24
3/	0,5 (0,1) λ=632,8 nm		3/	0,5 (0,1) λ=632,8 nm
4/	-		4/	2,18'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION		
ROHS: COMPLIANT	SCALE: NONE			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	25mm Dia x 50mm FL, 355nm Laser Grade V-Coat Coated, Plano-Convex
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN:	mm
INDICATIONS IN ACCORDANCE WITH ISO 10110				38765 SHEET SIZE A4 SHEET 1 OF 1