



FOCAL LENGTH (EFL):  $-12 \pm 0,12$   
 BACK FOCAL LENGTH (BFL):  $-12,99$

1 AR COATING: NONE

| LEFT SURFACE |                            | MATERIAL            | RIGHT SURFACE |                            |
|--------------|----------------------------|---------------------|---------------|----------------------------|
| R            | $6,2 \pm 0,006$ CV         | GLASS N-BK7 517/642 | R             | $\infty$ PL                |
| Øe           | 5,4                        |                     | Øe            | 5,4                        |
| 3/           | 3 (0,5) $\lambda=632,8$ nm |                     | 3/            | 3 (0,5) $\lambda=632,8$ nm |
| 4/           | -                          |                     | 4/            | 1,93'                      |
| 5/           | 40 - 20 (MIL-PRF-13830B)   |                     | 5/            | 40 - 20 (MIL-PRF-13830B)   |
| 6/           | -                          |                     | 6/            | -                          |

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT    SCALE: NONE     $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 6,0mm Dia, x -12 FL, Uncoated, Plano-Concave Lens

DWG NO 45008

SHEET SIZE A4    SHEET 1 OF 1