



FOCAL LENGTH (EFL): 25,4 ± 0,25  
 BACK FOCAL LENGTH (BFL): 21,48

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	19,93±0,02 CX	GLASS N-SF11 785/258	R	∞ PL
Øe	24,4		Øe	24,4
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,27'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT    SCALE: NONE    λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 25,4mm Dia, x 25,4mm FL, Uncoated, Plano-Convex Lens

DWG NO 49847

SHEET SIZE A4    SHEET 1 OF 1