

FOCAL LENGTH (EFL): $-18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): $-19,37$

1 AR COATING: NONE

| LEFT SURFACE | | MATERIAL | RIGHT SURFACE | |
|--------------|--------------------------|----------------------------|---------------|--------------------------|
| R | 8,25±0,008 CV | GLASS FUSED SILICA 458/678 | R | ∞ PL |
| Øe | 8,1 | | Øe | 8,1 |
| 3/ | 3 (0,5) λ=632,8 nm | | 3/ | 3 (0,5) λ=632,8 nm |
| 4/ | - | | 4/ | 2,18' |
| 5/ | 40 - 20 (MIL-PRF-13830B) | | 5/ | 40 - 20 (MIL-PRF-13830B) |
| 6/ | - | | 6/ | - |

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 9,0mm Dia, x -18 FL, Uncoated, UV Plano-Concave Lens

DWG NO 45701

SHEET SIZE A4 SHEET 1 OF 1