

FOCAL LENGTH (EFL): 24 ±0,24  
 BACK FOCAL LENGTH (BFL): 23,31

- 1 AR COATING: UV-AR  
 R(ABS) ≤ 1,0% FROM 250-425nm @ 0° AOI  
 R(AVG) ≤ 0,75% FROM 250-425nm @ 0° AOI  
 R(AVG) ≤ 0,5% FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	21,69±0,022 CX	GLASS FUSED SILICA 458/678	R	21,69±0,022 CX
Øe	5,4		Øe	5,4
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT  
 SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 6mm Dia, x 24mm FL, UV-AR Coated, UV Double-Convex Lens

DWG NO 49988

SHEET SIZE A4 SHEET 1 OF 1