



FOCAL LENGTH (EFL): 200 ±2
 BACK FOCAL LENGTH (BFL): 198,84

- 1 AR COATING: UV-AR
 - R(ABS) ≤ 1,0% FROM 250-425nm @ 0° AOI
 - R(AVG) ≤ 0,75% FROM 250-425nm @ 0° AOI
 - R(AVG) ≤ 0,5% FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	182,851±0,183 CX	GLASS FUSED SILICA 458/678	R	182,851±0,183 CX
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION			
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	25mm Dia, x 200mm FL, UV-AR Coated, UV Double-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN:	DWG NO	48311
INDICATIONS IN ACCORDANCE WITH ISO 10110		mm			SHEET 1 OF 1