



FOCAL LENGTH (EFL): $-50 \pm 0,5$
 BACK FOCAL LENGTH (BFL): $-50,85$

1 AR COATING: NONE

| LEFT SURFACE | | MATERIAL | RIGHT SURFACE | |
|--------------|----------------------------|----------------------------|---------------|----------------------------|
| R | 46,236±0,046 CV | GLASS FUSED SILICA 458/678 | R | 46,236±0,046 CV |
| Øe | 24 | | Øe | 24 |
| 3/ | 3 (0,5) $\lambda=632,8$ nm | | 3/ | 3 (0,5) $\lambda=632,8$ nm |
| 4/ | - | | 4/ | 2,18' |
| 5/ | 40 - 20 (MIL-PRF-13830B) | | 5/ | 40 - 20 (MIL-PRF-13830B) |
| 6/ | - | | 6/ | - |

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

25mm Dia, x -50mm FL, Uncoated, UV DCV Lens

DWG NO

48327

SHEET SIZE
A4

SHEET
1 OF 1