




NOTES:

- SUBSTRATE MATERIAL:  
Fused Silica
- SURFACE S1 TO BE PARALLEL TO SURFACE S2 TO WITHIN <3 ARCMIN
- COATING (APPLY ACROSS COATING APERTURE)  
S1: Square Aluminum (AlMgF2) Apertures  
R: 30±5% @ 250 - 2000 nm @ 45° AOI  
T: 70±5% @ 250 - 2000 nm @ 45° AOI  
S2: NONE
- POLKA DOT CENTER TO CENTER SPACING : 0.15 mm  
POLKA DOT MINIMUM APERTURE: 2mm
- ROHS : COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	34.2 x 34.2	34.2 x 34.2
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm

**EO**® **Edmund Optics**®

TITLE

38.0mm Sq 30R/70T, UV-NIR Polka-Dot  
Beamsplitter

DWG NO

18720

SHEET  
1 OF 1