



FOCAL LENGTH (EFL):  $15 \pm 0,15$   
 BACK FOCAL LENGTH (BFL): 13,37

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	13,01±0,013 CX	GLASS FUSED SILICA 458/678	R	13,01±0,013 CX
Øe	11		Øe	11
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 12mm Dia, x 15mm FL, Uncoated, UV Double-Convex Lens

DWG NO 49244

SHEET SIZE A4 SHEET 1 OF 1