NOTES:

1. SUBSTRATE: N-BK7


2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN


3. COATING (APPLY ACROSS CLEAR APERTURE)


   S1: VIS 0° (425-675nm)
   S2: VIS 0° (425-675nm)
   Ravg ≤0.4% @ 425 - 675nm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT







FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	∅22.86	∅22.86
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE: 25.4mm Dia., 1mm Thick, VIS 0° Coated λ/4 N-BK7 Window

DWG NO 23385