



NOTES:

1. SUBSTRATE: SILICON (SI)
2. COATING

S1 & S2:
R(AVG) <1% @ 1650 - 3000nm
R(ABS) <2% @ 1650 - 3000nm


3. EDGES: DIAMOND TURNED
4. CENTERING, ETD: <21.8 µm
5. RoHS: COMPLIANT
6. ASPHERIC SURFACE DESCRIBED BY THE FOLLOWING
EQUATION AND COEFFICIENTS SHOWN IN TABLE BELOW

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



COEFFICIENT TABLE	
COEFFICIENT	S1
k	-1.712056E+00
D	0.000000E+00
E	0.000000E+00
F	0.000000E+00
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	CONVEX	CONCAVE	EFL @ 4000nm: 25			
RADIUS	26.922	43.582	BFL @ 4000nm: 22.5			
SURFACE ACCURACY	<0.3µm	N/A	THIRD ANGLE PROJECTION 			
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	90%	90%	TITLE			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	25mm Dia x 25mm FL BBAR (1650-3000nm) Coated, Si Aspheric Lens			
			ALL DIMS IN	mm	DWG NO	SHEET
					24289	1 OF 1

 **Edmund Optics®**