





FOCAL LENGTH (EFL): 40 ±0,4
BACK FOCAL LENGTH (BFL): 35,13

1 532nm V-COAT
R(ABS) < 0,25% @ 532nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 31,389 CX Øe 39 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 39 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 1,27' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®					
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 40mm Dia x 40mm FL, 532nm V-Coat Coated, Plano-Convex Lens					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm				DWG NO 26137		SHEET T SIZE A4	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING										
INDICATIONS IN ACCORDANCE WITH ISO 10110										