


1030nm TECHSPEC Low GDD Dielectric Ultrafast Laser Mirrors

Coating Specification:

R(avg) S & P >99.90% @ 1030nm @ 45° AOI

R(avg) >99.7% @ 990 - 1070nm @ 45° AOI

Theoretical Reflection Curve



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED


1030nm TECHSPEC Low GDD Dielectric Ultrafast Laser Mirrors

GDD Specification:

$\pm 10 \text{ fs}^2$ @ 990 – 1070nm @ 45° AOI (s-pol)

$\pm 30 \text{ fs}^2$ @ 1010 – 1050nm @ 45° AOI (p-pol)

Theoretical GDD Curve



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED