




f': 12 ± 0,12

BACK FOCAL LENGTH (BFL): 10



LEFT SURFACE			MATERIAL	RIGHT SURFACE					
R 6,2 CX Øe 7,2 ⌂ AR Rave(400nm - 700nm, 0°) < 1,75% 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ - 			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 7,2 ⌂ AR Rave(400nm - 700nm, 0°) < 1,75% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 					
PROTECTIVE CHAMFERS AS NEEDED <table><tr><td>ROHS: COMPLIANT</td><td>SCALE: NONE</td><td>λ = 587,6nm</td></tr></table> SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110				ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	FIRST ANGLE PROJECTION 	 Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
			TITLE 8mm Dia x 12mm FL, MgF2 Coated, Plano-Convex Lens						
			DWG NO 71328	SHEET SIZE A4	SHEET 1 OF 1				