

[All Products](#) / [Optomechanics](#) / [Manual Translation Stages and Slides](#) / [Manual Stages and Slides](#)

Metric Lab Jacks




- Rugged, Black Anodized Aluminum Construction
- Fine Lead Screw for Precision Movement
- Large Adjustment Knob for Maximum Control
- Locking Knob to Secure Vertical Positioning

Common Specifications


Physical & Mechanical Properties			
Type of Movement:	Linear (Z)	Guide System:	Pantograph
Construction:	Aluminum, Brass, & Stainless	Leadscrew Pitch (mm):	1
Parallelism (mm):	0.1 (typical)		
Hardware & Interface Connectivity			
Type of Drive:	Lead Screw		

Technical Information

#54-687



#62-009 220MM X 160MM METRIC LAB JACK



Technical drawing showing three views of a mechanical component with dimensions and callouts:

- Top View:**
 - Overall width: 80
 - Overall length: 150 (25 + 25 + 25 + 25 + 25 + 25)
 - Callout: (15) M4 x 0.7
 - End view: Ø45, 80
- Front View:**
 - Overall width: 43 Max
 - Overall length: 160
 - Callouts: Min 63, Max 85, 14, 132, 52 Max, 10, 10
- Bottom View:**
 - Overall width: 60
 - Overall length: 140
 - Callouts: (4) M6 x 1.0, (4) Ø7 c'bore, (4) Ø4.5 c'bore, 50, 50

Units: mm

Products

Stage Size (mm)	Type	Height Adjustment (mm)	Minimum Height (mm)	Maximum Height (mm)	Load Capacity (kg)	Stock Number	Price	Buy
Top: 132 x 80 Bottom: 160 x 80	Metric	22	63	85	20	#56-336	€777,65	4 In Stock
160 x 100	Universal (Metric & English)	42	81	123	25	#54-687	€937,30	8 In Stock
220 x 160	Metric	70	100	170	30	#62-009	€1.112,40	5 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
Phone: 1-800-363-1992 :
www.edmundoptics.com