


[All Products](#) / [Optics](#) / [Optical Filters](#) / [Neutral Density \(ND\) Filters](#)

Stepped Neutral Density (ND) Filters



- 11 Discrete Density Steps
- Design Wavelength of 400 - 700nm
- Density Neutrality of $\pm 5\%$

Common Specifications


Physical & Mechanical Properties

Dimensions (mm):	25.4 x 50.8	Length (inches):	2.0
Length (mm):	50.80	Thickness (inches):	0.062
Width (inches):	1.0	Width (mm):	25.40

Optical Properties

Substrate:	Float Glass	Coating:	Stepped Variable
Blocking Wavelength Range (nm):	400 - 700		

Technical Information



Products

Dimensions (mm)	Optical Density OD (Average)	Thickness (inches)	Stock Number	Price	Buy
25.4 x 50.8	0.04 - 1.0	0.062	#32-599	€202,91 Volume Pricing	2 In Stock
25.4 x 50.8	0.04 - 2.0	0.062	#64-383	€223,51 Volume Pricing	4 In Stock
25.4 x 50.8	0.04 - 3.0	0.062	#64-384	€246,17 Volume Pricing	3 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com