

[All Products](#) / [Cameras](#) / [USB Cameras](#)

CamIR 1550nm NIR USB 3.1 Cameras



- 1550nm Designed Wavelength
- Phosphor Coated Camera Sensor
- Includes Camera, Cable, and Easy-to-Use Software

Common Specifications

General

Manufacturer:	Scintacor
---------------	-----------

Physical & Mechanical Properties

Housing:	Full
----------	------

Sensor

Type of Sensor:	Progressive Scan CMOS	Type of Shutter:	Global
-----------------	-----------------------	------------------	--------

Hardware & Interface Connectivity

Video Output:	USB 3.1	Connector:	USB 3.1
Power Supply:	Power over USB	GPIOs:	1 opto-isolated input, 1 opto-isolated output, 1 non-isolated bi-directional, 1 non-isolated input
Synchronization:	Hardware Trigger (GPIO) or Software Trigger	Interface Port Orientation:	Back Panel
GPIO Connector Type:	7-pin JST		

Environmental & Durability Factors

Operating Temperature (°C):	0 to 50
Storage Temperature (°C):	-30 to +60

Technical Information

Products

Type	Camera Sensor Format	Resolution (MegaPixels)	Connector	Mount	Housing	Stock Number	Price	Buy
NIR Camera	1/2.9"	1.60	USB 3.1	CS-Mount	Full	#29-547	€4.510,00	In Stock
NIR Camera	2/3"	2.80	USB 3.1	C-Mount	Full	#29-548	€6.510,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com