

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

Olympus X-Line Extended Apochromat Infinity Corrected Objectives

See More by [Olympus](#)



- High Numerical Aperture (NA) up to 1.45
- Chromatic Aberration Correction from 400 - 1000nm
- Uniform Image Flatness over Large FOVs

Common Specifications

General

Compatible Tube Lens
Focal Length (mm):

Focal Length: 180mm

Manufacturer:

Olympus

Optical Properties

Wavelength Range (nm): 400 - 1000

Field Number (mm): 26.5

Threading & Mounting

Mounting Threads:

RMS / 20.32mm x 36 TPI

Technical Information

Products

Magnification	NA	Field Number (mm)	Focal Length FL (mm)	Model Number	Working Distance (mm)	Stock Number	Price	Buy
4X	0.16	26.5	45.00	UPLXAPO4X	13.0	#14-905	€2.540,00	5 In Stock
10X	0.40	26.5	18.00	UPLXAPO10X	3.1	#14-906	€3.485,00	Contact Us
20X	0.80	26.5	9.00	UPLXAPO20X	0.61	#14-907	€4.530,00	5 In Stock
40X	0.95	26.5	4.50	UPLXAPO40X	0.18	#14-908	€5.880,00	Contact Us
40X	1.40	26.5	4.50	UPLXAPO40XO	0.13	#73-283	€8.830,00	1 In Stock
60X	1.20	26.5	3.00	UPLXAPO60XW	0.28	#74-022	€9.180,00	1 In Stock
60X	1.42	26.5	3.00	UPLXAPO60XO	0.15	#14-909	€9.410,00	4 In Stock
100X	1.45	26.5	1.80	UPLXAPO100XO	0.135	#14-910	€9.560,00	1 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
Phone: 1-800-363-1992 ;
www.edmundoptics.com