

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

## Teledyne DALSA Genie™ Nano 5GigE Cameras See More by [Teledyne DALSA](#)



- 5GBASE-T (5GigE) Ethernet Interface
- 3.2 to 12.4 Megapixel Sensors
- TurboDrive™ Technology for Data Transfer Speeds up to 985 MB/s
- Compact (32 x 44 x 59mm), Lightweight, and Robust Design



### Common Specifications

#### General

<b>Manufacturer:</b>	Teledyne DALSA	<b>Camera Series:</b>	Genie Nano-5GigE
----------------------	----------------	-----------------------	------------------

#### Physical & Mechanical Properties

<b>Housing:</b>	Full
-----------------	------

#### Sensor

<b>Image Buffer:</b>	450MB
----------------------	-------

<b>Type of Sensor:</b>	Progressive Scan CMOS
------------------------	-----------------------

<b>Shutter Type:</b>	Global
----------------------	--------

<b>Exposure Time:</b>	Automatic, Programmable, or via External Trigger
-----------------------	--

<b>Machine Vision Standard:</b>	GigE Vision v2.0
---------------------------------	------------------

#### Electrical

<b>Power Consumption (W):</b>	9.4 - 9.6
-------------------------------	-----------

#### Hardware & Interface Connectivity

<b>Interface:</b>	5GigE (PoE)
-------------------	-------------

<b>Connector:</b>	5GigE, RJ45 with Screw Locks
-------------------	------------------------------

<b>Interface Port Orientation:</b>	Back Panel
------------------------------------	------------

#### Threading & Mounting

<b>Mounting Threads:</b>	1/4-20 with Tripod Mount Adapter <a href="#">#34-966</a>
--------------------------	--

#### Environmental & Durability Factors

<b>Operating Temperature (°C):</b>	-20 to +65
------------------------------------	------------

**Technical Information**

Products

Type	Model Number	Sensor Format	Resolution (Megapixels)	Connector	Mount	Stock Number	Price	Buy
Monochrome Camera	Nano-5G-M2050	1/1.8"	3.20	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-024</a>	€1.596,00	5 In Stock
Color Camera	Nano-5G-C2050	1/1.8"	3.20	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-025</a>	€1.617,00	1 In Stock
Monochrome Camera	Nano-5G-M2450	2/3"	5.10	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-026</a>	€1.827,00	1 In Stock

*Typically 1-2 Recertified Products are in stock at a time. Please contact our sales team if you would like exact availability of an item.*

- Open Box – Missing original packaging
- Cosmetic Blemishes – Scratches, rub marks or other minor cosmetic imperfections
- Service/Repair – Product has been serviced to the factory original specification
- Factory Returns – Product has been returned in its original condition

View all our [recertified products](#) in the Web Specials section of our website.

Monochrome Camera	Nano-5G-M2450	2/3"	5.10	5GigE, RJ45 with Screw Locks	C-Mount	Recertified products are inspected for damage and any necessary repairs are	€1.277,02	1 In Stock
-------------------	---------------	------	------	------------------------------	---------	---	-----------	------------

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual and Large Accessory		

Color Camera	Nano-5G-C2450	2/3"	5.10	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-027</a>	€1.843,00	1 In Stock
Monochrome Camera	Nano-5G-M4060	1"	8.90	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-030</a>	€2.972,00	1 In Stock
Color Camera	Nano-5G-C4060	1"	8.90	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-031</a>	€2.993,00	14 In Stock
Monochrome Camera	Nano-5G-M4040	1.1"	12.40	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-028</a>	€3.145,00	7 In Stock
Color Camera	Nano-5G-C4040	1.1"	12.40	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-029</a>	€3.161,00	Contact Us
Monochrome Camera	G5-GM31-M8105	Super 35MM Format	44.40	5GigE, RJ45 with Screw Locks	M42-Mount	<a href="#">#28-676</a>	€6.468,00	1 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)