


[All Products](#) / [Laser Optics](#) / [Laser Mirrors](#) / [Laser Line Mirrors](#)
TECHSPEC® 920nm Laser Line Mirrors


- >99.8% Absolute Reflectivity at 920nm
- 99.5% Average Reflectivity in the 905 - 935nm Range
- High Laser Damage Threshold
- Wide Range of Laser Line Mirrors Options Available

Common Specifications

Physical & Mechanical Properties

Back Surface:	Commercial Polish	Clear Aperture (%):	90
Parallelism (arcmin):	<3		

Optical Properties

Wavelength Range (nm):	905 - 935		
Substrate:	Fused Silica (Corning 7980)	Coating:	Laser Mirror (905-935nm)
Surface Flatness (P-V):	$\lambda/10$	Surface Quality:	10-5

Technical Information

Products

Title	Stock Number	Price	Buy
920nm Laser Line Mirror, 45° AOI, 12.7mm Dia., 6.35mm Thick	#27-557	€131,00	3-4 days
920nm Laser Line Mirror, 45° AOI, 25.4mm Dia., 6.35mm Thick	#27-558	€155,00	3-4 days
920nm Laser Line Mirror, 45° AOI, 50.8mm Dia., 9.53mm Thick	#27-559	€278,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com