

[All Products](#) /
 [Optics](#) /
 [Optical Lenses](#) /
 [Aspheric Lenses](#) /
 [Glass Molded](#)

Rochester Precision Optics (RPO) Infrared Molded Glass Aspheric Lenses



- Precision Infrared Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Constructed with IG6 Infrared Glass Substrates

Common Specifications

Physical & Mechanical Properties

Bevel:

Protective bevel as needed

Optical Properties

Substrate:

IG6

Coating:

BBAR (800-1200)

Coating Specification:

$R_{avg} < 1\%$ @ 800 - 1200, 0
- 30° AOI

Surface Quality:



80-60

**Wavelength Range
(nm):**

800 - 1200

Technical Information

Products

Title	Stock Number	Price	Buy
#73-677 New			
0.40 NA, 4.0mm FL, RPO IR Molded Glass Aspheric Lens	 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€125,00	3-4 days
#73-679 New			
0.42 NA, 6.5mm FL, RPO IR Molded Glass Aspheric Lens	 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€125,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com