

Optotune -2 to +3 Diopter, M42 x 1.0 to M42 x 1.0 Focus Tunable Lens | EL-16-40-TC-VIS-5D-M42

See More by [Optotune](#)



Stock **#33-495** CLEARANCE 3-4 DAYS

-

1

+

€1.369^{.00}

ADD TO CART

Qty 1+
€1.369,00
Volume Pricing
Request Quote
! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Specialty Lens

Type:

Driver:	
#88-940	
Lifecycles:	
1,000,000,000	
Model Number:	
EL-16-40-TC-MS-5D-M42	
Response Time (ms):	
5 (typical @ 30°C)	
Settling Time (ms):	
25 (typical @ 30°C)	
Physical & Mechanical Properties	
Clear Aperture CA (mm):	
16.00	
Dimensions (mm):	
47.0 x 70.0	
Thickness (mm):	
30.10	
Optical Properties	
Substrate: ☐	
Low Dispersion Polymer	
Coating:	
BBAR (420-950nm)	
Wavelength Range (nm):	
420 - 950	
Abbe Number (v _d):	
100.00	
Focus Range:	
-2 to +3 diopter -500 to +333mm	
Index of Refraction (n _d):	
1.3	
Transmitted Wavefront Error, RMS:	
Vertical: 0.25λ @ 525nm Horizontal: 0.50λ @ 525nm	
Electrical	
Current (mA):	
-250 to 250	
Power Consumption (W):	
0 - 0.7	
Threading & Mounting	
Mounting Threads:	
M42 x 1.0 (Male) M42 x 1.0 (Female)	
Environmental & Durability Factors	
Operating Temperature (°C):	
-20 to +65	
Regulatory Compliance	
RoHS:	
Compliant	
Certificate of Conformance:	
View	

PRODUCT DETAILS

- Multiple Imaging Lens Mounting Options
- Large Clear Aperture Ideal for Machine Vsion Applications
- Industrial Hirose Connection with Temperature Sensing
- Integrated Temperature Control for Improved Thermal Effects
- [Optotune Focus Tunable Lenses 10mm Clear Aperture Hirose Connector](#) and [Lens Drivers](#) Also Available

Optotune Focus Tunable Lenses 16mm Clear Aperture Hirose Connector eliminate the need for optomechanical subsystems otherwise required to alter the focal length of your imaging application. They feature large clear apertures and are offered in many popular machine vision mounting options, making them ideal for inspection and detection systems. These lenses offer continuous focusability from -2 to +3 diopters controlled by an industrial Hirose connection. Optotune Focus Tunable Lenses 16mm Clear Aperture Hirose Connector exhibit no autofluorescence, reducing unwanted light on the detector and feature integrated temperature sensing to provide open loop reproducibility typically within 0.1 diopters. The lenses are made of low dispersion polymer and feature a broadband anti-reflection coating.

Note: Hirose cables, available in 1m length ([#88-941](#)), 3m length ([#33-468](#)) or 5m length ([#23-852](#)), and Lens Driver ([#88-940](#)) are required and sold separately. The Gardasoft TR-CL180 Industrial Lens Controller ([#13-803](#)) is an optional accessory that provides repeatable, precision control of Optotune Industrial Focus-Tunable Lenses. Prescription data is available to model the effect an offset lens has on overall focal range.

TECHNICAL INFORMATION

