

LightPath 354560 | 6.33mm Dia., 0.18 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#46-372** **20+ In Stock**

-

1

+

€85^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	€85,00 each
Qty 11-49	€76,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

354560


Lightpath Lens Code:

Aspheric Lens	Type:
Collimate or Focus Laser Light	Typical Applications:
Physical & Mechanical Properties	
6.33 ±0.015	Diameter (mm):
5.10	Clear Aperture CA (mm):
2.280	Edge Thickness ET (mm):
2.77 ±0.05	Center Thickness CT (mm):
Protective as needed	Bevel:
Optical Properties	
13.86 @ 650nm	Effective Focal Length EFL (mm):
0.18	Numerical Aperture NA:
D-ZK3	Substrate: 
±1	Focal Length Tolerance (%):
650	Aspheric Design Wavelength (nm):
BBAR (600-1050nm)	Coating:
R _{avg} <1.0% @ 600 - 1050nm	Coating Specification:
40-20	Surface Quality:
2.78	f/#:
600 - 1050	Wavelength Range (nm):
12.11	Working Distance (mm):
Infinite	Conjugate Distance:
< 0.07	Transmitted Wavefront Error (λ, RMS):
Environmental & Durability Factors	
≤200	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



TECHNICAL INFORMATION

