

NOTES:

1. SUBSTRATE:
NITROCELLULOSE

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: METAL/DIELECTRIC


40% R @ 400 - 700nm @ 45° AOI

40% T @ 400 - 700nm @ 45° AOI



R/T TOLERANCE: ±3%

S2: NONE

3. ROHS COMPLIANT



SECTION A-A



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø 203.2	Ø 203.2
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN

mm

EO® Edmund Optics®

TITLE

203.2mm Clear Aperture 40R/40T, Pellicle
Beamsplitter

DWG NO

22590

SHEET
1 OF 1