

0.19 - 20µm, 250W, VIS/NIR/CO₂ Portable Laser Power Meter



0.19 - 20µm, 250W, VIS/NIR/CO2 Portable Laser Power Meter

Stock #78-471 NEW 1 In Stock

-

1

+

€1.520⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€1.520,00 each
Qty 5+	€1.360,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
17	Operating Lifetime (hours):
1.50	Response Time (s):
Touch screen color LCD	Type of Display:
USB Port Available for Data Transfer	Note:

Physical & Mechanical Properties	
181.40	Length (mm):
210	Weight (g):
59.00	Width (mm):
17.00	Depth (mm):
Optical Properties	
248 - 10600	Wavelength Range (nm):
0.248 - 10.6	Wavelength Range (µm):
0.193 - 20µm	Spectral Range:
0.248 -10.6µm	Calibrated Spectral Range:
Sensor	
5s	Exposure Time:
Electrical	
10	Noise Equivalent Power (mW):
Hardware & Interface Connectivity	
USB Rechargeable Battery	Power Supply:
Threading & Mounting	
2 x 8-32	Mounting Hole for Screw:
Environmental & Durability Factors	
65	Maximum Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Small Portable Design with Touchscreen Display
- Computer and Software Not Required
- High Damage Threshold
- USB Rechargeable Battery

Touchscreen Portable Laser Power Meters feature LCD displays with touchscreen controls, the ability to adjust wavelength, brightness and screen orientation, and min/max display. Available in two designs, one as a silicon based sensor and the other an absorber, these portable power meters can transfer data to a computer for data logging via a mini USB port. The silicon sensor model (#34-514) features a folding body design with a click stop at 90 degrees, providing the unique ability of being placed on an optical table unmounted when oriented at 90 degrees. If the beam height is 78mm off the optical table, you can simply set the folded power meter directly onto the table. Both Touchscreen Portable Laser Power Meter models feature 8-32 mounting holes for table top mounting and rechargeable battery.

Note: Mini-USB cable not included.