

LightPath 354059 | 6.33mm Dia., 0.19 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-693** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

€65,00

ADD TO CART

Qty 1-10

€65,00

Qty 11+

€57,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):

6.33 ±0.015

Effective Focal Length EFL (mm):

14.00 @633nm

Numerical Aperture NA:

0.19

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 60-40
Clear Aperture CA (mm): 5.20
Edge Thickness ET (mm): 1.73
Center Thickness CT (mm): 2.35 ±0.05
f/#: 2.63
Bevel: Protective bevel as needed
Lightpath Lens Code: 354059
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Working Distance (mm): 12.600
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant