





FOCAL LENGTH (EFL): 35 ±0,35
BACK FOCAL LENGTH (BFL): 29,17

- 1 NIR I
R(AVG) ≤ 0,5% FROM 600 - 1050nm @ 0° AOI

LEFT SURFACE			MATERIAL		RIGHT SURFACE			
R 16,045 CX			GLASS Fused Silica 458/678 Nd: 1,458		R ∞ PL			
Øe 24					Øe 24			
⌂ SEE NOTE 1					⌂ SEE NOTE 1			
3/ 3 (0,5) λ=632,8 nm					3/ 3 (0,5) λ=632,8 nm			
4/ -					4/ 2,18'			
5/ 40 - 20					5/ 40 - 20			
6/ -			6/ -					
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®			
ROHS: COMPLIANT		SCALE: NONE						λ = 587,6nm
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE 25mm Dia x 35mm FL, NIR I Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26072	SHEET T SIZEA4	SHEET 1 OF 1