





FOCAL LENGTH (EFL): $12 \pm 0,12$
 BACK FOCAL LENGTH (BFL): $10,63$

- 1 1550nm V-COAT
 R(ABS) < 0,25% @ 1550nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,5 CX			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL		
Øe 5,4				Øe 5,4		
SEE NOTE 1				SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 2,18'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	6mm Dia x 12mm FL, 1550NM V- COAT Coated, Plano-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	25887
					SHEET T SIZE	A4
					SHEET 1 OF 1	