

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

LightPath 354062 | 6mm Dia., 0.24 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock #83-705 CLEARANCE 3-4 DAYS
[Other Coating Options](#)

1 **€22,95**

ADD TO CART

Qty 1+

€22,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
6.00 ±0.015

Effective Focal Length EFL (mm):
11.00 @ 633nm

Numerical Aperture NA:
0.24

Substrate: [D-ZK3](#)

Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 100-60
Clear Aperture CA (mm): 5.20
Edge Thickness ET (mm): 1.53
Center Thickness CT (mm): 2.25 ±0.05
f/#: 2.08
Bevel: Protective bevel as needed
Lightpath Lens Code: 354062
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Working Distance (mm): 9.700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant