



[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [UV and IR Windows](#)
TECHSPEC® Germanium (Ge) Windows


- Uncoated or with AR Coatings Designed for a Variety of IR Ranges
- Minimal Chromatic Aberration Due to Low Dispersion
- Ideal for Infrared Applications Requiring Rugged Optics
- [DLC Coated Germanium Windows](#) are also Available
- Due to material supply chain disruptions with germanium, there may be increased lead times and price changes on our germanium products. For more information, please contact our [customer service team](#).
- Edmund Optics has limited remaining inventory of this part number and no raw material available to supply more once this is depleted. Please contact our Product Support Engineers to help with an alternate solution for your needs. Customer Service can provide you the latest price and availability.

Common Specifications

| | | | |
|---|----------------------|--|--------|
| Bevel: | Protective as needed | Poisson's Ratio: | 0.28 |
| Young's Modulus (GPa): | 102.7 | Knoop Hardness (kg/mm²): | 780.00 |
| Substrate: | Germanium (Ge) | | |
| Density (g/cm³): | 5.33 | | |
| Coefficient of Thermal Expansion CTE (10⁻⁶/°C): | 6.1 | | |

Technical Information



Products

| Dia. (mm) | Thickness (mm) | Coating | Stock Number | Price | Buy |
|-----------|----------------|---------------------------|-------------------------|---------|--------------|
| 5.00 | 1.00 | Uncoated | #20-167 | €312,00 | 20+ In Stock |
| 10.00 | 1.50 | BBAR (3000-5000nm) | #89-558 | €530,00 | 10 In Stock |
| 10.00 | 1.50 | BBAR (8000-12000nm) | #47-685 | €530,00 | 20+ In Stock |
| 12.50 | 1.00 | Uncoated | #83-341 | €424,00 | 20+ In Stock |
| 12.50 | 1.00 | BBAR (8000-12000nm) | #83-353 | €580,00 | 20+ In Stock |
| 12.50 | 2.00 | BBAR (8000-12000nm) | #47-686 | €590,00 | 20+ In Stock |
| 12.50 | 3.00 | Uncoated | #83-342 | €590,00 | 13 In Stock |
| 12.70 | 3.00 | Uncoated | #74-430 | €478,00 | 4 In Stock |
| 12.70 | 3.00 | AR Coated: 7 - 12 μ m | #74-433 | €600,00 | 5 In Stock |
| 20.00 | 2.00 | Uncoated | #68-736 | €520,00 | 20+ In Stock |
| 20.00 | 2.00 | BBAR (3000-5000nm) | #89-562 | €685,00 | 14 In Stock |
| 20.00 | 2.00 | BBAR (8000-12000nm) | #63-213 | €685,00 | 4 In Stock |
| 25.00 | 1.00 | BBAR (8000-12000nm) | #83-355 | €910,00 | 1 In Stock |
| 25.00 | 2.00 | BBAR (3000-5000nm) | #89-564 | €850,00 | 5 In Stock |
| 25.00 | 2.00 | BBAR (8000-12000nm) | #83-356 | €925,00 | 2 In Stock |
| 25.00 | 3.00 | Uncoated | #68-737 | €610,00 | 3 In Stock |
| 25.00 | 3.00 | BBAR (3000-5000nm) | #89-565 | €870,00 | 12 In Stock |
| 25.00 | 5.00 | Uncoated | #23-139 | €650,00 | 20+ In Stock |
| 25.40 | 3.00 | Uncoated | #11-862 | €575,00 | 7 In Stock |

| | | | | | |
|--------|------|-----------------------|-------------------------|-----------|--------------|
| 25.40 | 3.00 | BBAR (3000-5000nm) | #11-865 | €870,00 | 1 In Stock |
| 25.40 | 5.00 | Uncoated | #74-431 | €610,00 | 8 In Stock |
| 25.40 | 5.00 | AR Coated: 1.9 - 6 µm | #74-432 | €870,00 | 3 In Stock |
| 30.00 | 1.00 | Uncoated | #23-140 | €725,00 | 3 In Stock |
| 40.00 | 2.00 | Uncoated | #23-141 | €1.090,00 | 20+ In Stock |
| 40.00 | 2.00 | BBAR (8000-12000nm) | #23-156 | €1.410,00 | 6 In Stock |
| 40.00 | 4.00 | Uncoated | #68-739 | €1.165,00 | 3 In Stock |
| 40.00 | 4.00 | BBAR (3000-5000nm) | #89-567 | €1.410,00 | 3 In Stock |
| 50.00 | 1.00 | BBAR (3000-5000nm) | #89-568 | €1.755,00 | 5 In Stock |
| 50.00 | 2.00 | BBAR (3000-5000nm) | #89-569 | €1.780,00 | 7 In Stock |
| 50.00 | 3.00 | Uncoated | #68-740 | €1.435,00 | 16 In Stock |
| 50.00 | 3.00 | BBAR (3000-12000nm) | #62-646 | €1.415,00 | 7 In Stock |
| 50.00 | 3.00 | BBAR (8000-12000nm) | #47-688 | €1.955,00 | 16 In Stock |
| 76.20 | 5.00 | BBAR (3000-5000nm) | #11-867 | €3.205,00 | 4 In Stock |
| 100.00 | 6.00 | Uncoated | #17-669 | €5.170,00 | 1 In Stock |



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com