

[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Linear Polarizers](#) / [Absorptive \(Dichroic\) Polarizers](#) / [Laminated Film Polarizers](#)

NIR Glass Linear Polarizers



- Ideal for Fiber Optic and Laser Applications
- 750 – 850nm and 1000 – 2000nm Wavelength Ranges
- 1000:1 Extinction Ratio

Common Specifications



Physical & Mechanical Properties

Thickness (mm):	2.00 ±0.2	Parallelism (arcmin):	<4
Dimensional Tolerance (mm):	+0.0/-0.2	Construction:	Dichroic Polarizing Film on Glass

Optical Properties

Extinction Ratio:	1000:1	Substrate:	Polymer Film on B270
Transmission Tolerance (%):	±3		

Technical Information



Products

Extinction Ratio	Wavelength Range (nm)	Dia. (mm)	Dimensional Tolerance (mm)	Thickness (mm)	Parallelism (arcmin)	Stock Number	Price	Buy
1000:1	750 - 850	12.50	+0.0/-0.2	2.00	<4	#48-891	€306,94 Volume Pricing	20+ In Stock
1000:1	750 - 850	25.00	+0.0/-0.2	2.00	<4	#48-892	€396,55 Volume Pricing	4 In Stock
1000:1	750 - 850	30.00	+0.0/-0.2	2.00	<4	#48-893	€396,55 Volume Pricing	6 In Stock
1000:1	750 - 850	50.00	+0.0/-0.2	2.00	<4	#48-894	€561,35 Volume Pricing	4 In Stock
1000:1	1000 - 2000	12.50	+0.0/-0.2	2.00	<4	#48-887	€306,94 Volume Pricing	5 In Stock
1000:1	1000 - 2000	25.00	+0.0/-0.2	2.00	<4	#48-888	€237,93 €396,55 Volume Pricing	6 In Stock
1000:1	1000 - 2000	30.00	+0.0/-0.2	2.00	<4	#48-889	€396,55 Volume Pricing	8 In Stock
1000:1	1000 - 2000	50.00	+0.0/-0.2	2.00	<4	#48-890	€561,35 Volume Pricing	7 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
 Phone: 1-800-363-1992 :
www.edmundoptics.com