

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

Olympus Super Long WD M Plan Achromat Infinity Corrected Objectives

 See More by [Olympus](#)


- Ideal for Brightfield Microscopy
- Ultra-Long Working Distances Reduce Risk of Specimen Damage
- Over 90% Transmission from 400 – 700nm
- Additional [Olympus Infinity Corrected Objectives](#) Available

Common Specifications

General

Compatible Tube Lens Focal Length (mm):	Focal Length: 180mm	Manufacturer:	Olympus
--	---------------------	----------------------	---------

Physical & Mechanical Properties

Maximum Diameter (mm):	26
-------------------------------	----

Optical Properties


Compatible Cover Glass Thickness (mm):	N/A		
Transmission (%):	T> 90 from 400-700nm	Wavelength Range (nm):	400 - 700
Field Number (mm):	26.5	Parfocal Length (mm):	45
Immersion Liquid:	N/A		

Threading & Mounting


Mounting Threads:	RMS / 20.32mm x 36 TPI
--------------------------	------------------------

Technical Information

Using Olympus Objectives with C-Mount Cameras



Typical Transmission



Products

Magnification	NA	Field Number (mm)	FL (mm)	Model Number	WD (mm)	Stock Number	Price	Buy
20X	0.25	26.5	9.00	1- U2M265	25.0	#86-824	€3.200,00	3-4 days
50X	0.35	26.5	3.60	1- U2M270	18.0	#86-825	€4.065,00	Contact Us
100X	0.60	26.5	1.80	1- U2M275	7.6	#86-826	€7.410,00	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com