

LightPath 355375 | 6.51mm Dia., 0.30 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-129** **20+ In Stock**

[Other Coating Options](#)

-

1

+

€69^{.53}

ADD TO CART

Volume Pricing	
Qty 1-10	€69,53 each
Qty 11-49	€61,80 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Thickness: 0.250 (t) (mm)

Compatible Window:

Material: BK7	
355375	Lightpath Lens Code:
Type:	
Aspheric Lens	
Typical Applications:	
Collimate or Focus Laser Light	
Physical & Mechanical Properties	
Diameter (mm):	
6.51 ±0.020	
Clear Aperture CA (mm):	
4.54	
Edge Thickness ET (mm):	
2.71	
Center Thickness CT (mm):	
3.19 ±0.04	
Bevel:	
Protective as needed	
Distance from Window to Lens (D) (mm):	
5.151	
Optical Properties	
Effective Focal Length EFL (mm):	
7.50 @ 780nm	
Numerical Aperture NA:	
0.3	
Substrate: 	
Focal Length Tolerance (%):	
±1	
Aspheric Design Wavelength (nm):	
780	
Coating:	
BBAR (350-700nm)	
Coating Specification:	
R _{avg} ≤0.5% @ 350 - 700nm	
Surface Quality:	
40-20	
f/#:	
1.67	
Wavelength Range (nm):	
350 - 700	
Working Distance (mm):	
5.8	
Conjugate Distance:	
Infinite	
Transmitted Wavefront Error (λ, RMS):	
< 0.05	
Environmental & Durability Factors	
Operating Temperature (°C):	
≤200	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	

PRODUCT DETAILS

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

TECHNICAL INFORMATION

