

0.33 NA, 10.0mm FL, HOYA Molded Glass Aspheric Lens

See More by [Hoya](#)



HOYAMolded Glass Aspheric Lenses

Stock #13-585 3-4 DAYS

- 1 + **€95,00**

ADD TO CART

Qty 1-10
€95,00

Qty 11+
€75,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
8.00 +0.00/-0.02

Effective Focal Length EFL (mm):
10.00 @ 780nm

Numerical Aperture NA:
0.33

Substrate: M-LaF81
Aspheric Design Wavelength (nm): 780
Coating: BBAR (680-880nm)
Coating Specification: R_{avg} <1% @ 680 - 880nm (typical)
Center Thickness CT (mm): 2.15
f/#: 1.25
Bevel: Protective bevel as needed
Type: Aspheric Lens
Wavelength Range (nm): 680 - 880
Working Distance (mm): 8.75
Conjugate Distance: 0
Transmitted Wavefront, RMS @ 632.8nm: 0.04λ
Model Number: A41_Z

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View