

[All Products](#) / [Optomechanics](#) / [Manual Translation Stages and Slides](#) / [Manual Stages and Slides](#)

TECHSPEC® High Load Capacity Dovetail Stages



- Compact Overall Size for System Integration
- Brass Construction for High Stiffness and up to 15kg Load Capacity
- Compatible with All TECHSPEC® Stages

Common Specifications

Physical & Mechanical Properties

Type of Movement:	Linear (X)	Guide System:	Dovetail
Drive Orientation:	Center Drive	Construction:	Matte Black Finish Brass
Leadscrew Pitch (mm):	0.5	Straight Line Accuracy (µm):	10

Hardware & Interface Connectivity

Type of Drive:	Lead Screw
----------------	------------

Technical Information

[illegible]

Products

Stage Size (mm)	Type	Type of Drive	Drive Orientation	Travel (mm)	Travel (inches)	Stock Number	Price	Buy
30 x 30	English	Lead Screw	Center Drive	8	0.31	#16-711	€114,00 Qty 10+ €100,60	3-4 days
40 x 40	English	Lead Screw	Center Drive	14	0.55	#16-712	€140,00 Qty 10+ €123,70	3-4 days
65 x 65	English	Lead Screw	Center Drive	25	0.98	#16-713	€187,00 Qty 10+ €164,70	3-4 days
30 x 30	Metric	Lead Screw	Center Drive	8	0.31	#16-714	€114,00 Qty 10+ €100,60	3-4 days
40 x 40	Metric	Lead Screw	Center Drive	14	0.55	#16-715	€140,00 Qty 10+ €123,70	3-4 days
65 x 65	Metric	Lead Screw	Center Drive	25	0.98	#16-716	€187,00 Qty 10+ €164,70	In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com