

[All Products](#) / [Optics](#) / [Prisms](#) / [Retroreflection Prisms](#)

TECHSPEC®

Mounted Fused Silica Corner Cube Retroreflectors




- 1/4-20 Tapped Holes for Easy Mounting
- Excellent Transmission in the UV
- Useful for Surveying and Alignment
- Also Available [Unmounted](#)

Common Specifications

Physical & Mechanical Properties				
Diameter Tolerance (mm):		+0.0/-0.1	Housing Tolerance (mm):	Outer Diameter: +0/-0.5, Height: ±0.25
Optical Properties				
Coating:		Aluminum with protective overcoat	Substrate:	Fused Silica (Corning 7980)
Surface Quality:		20-10	Image Orientation:	Left-Handed
Coating Specification:		Reflective Surfaces: R _{avg} >85% FROM 400-700nm, @ 45° AOI	Ray Deviation (°):	180
Wavelength Range (nm):		400 - 700	Power (fringes) @ 632.8nm:	0.20
Irregularity (fringes) @ 632.8nm:		0.20		
Threading & Mounting				
Mounting Threads:		(2) ¼-20 Tapped Holes		

Technical Information



Products

Inner Diameter (mm)	Coating	Stock Number	Price	Buy
12.7	Aluminum with protective overcoat	#15-818	€416,00 Qty 6+ €333,00	3-4 days
25.4	Aluminum with protective overcoat	#15-820	€468,00 Qty 6+ €374,00	Contact Us
50.8	Aluminum with protective overcoat	#15-822	€630,00 Qty 6+ €505,00	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com