

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [UV and IR Windows](#)

ISP Optics AMTIR-1 Windows





- Transmission from 750nm - 14μm
- Excellent Chemical Resistance to Acids
- Low Index of Refraction



Common Specifications

Physical & Mechanical Properties			
Bevel:	Protective as needed	Clear Aperture (%):	85
Clear Aperture CA (mm):	21.59	Diameter (mm):	25.40 +0.00/-0.13
Edges:	Fine Ground	Knoop Hardness (kg/mm ²):	170.00
Parallelism (arcmin):	<3	Poisson's Ratio:	0.21
Young's Modulus (GPa):	21.2		
Optical Properties			
Coating:	Uncoated		
Index of Refraction (n _d):	2.519 @ 3μm 2.503 @ 8μm 2.490 @ 12μm	Substrate:	AMTIR-1 (Ge ₃₃ As ₁₂ Se ₅₅)
Surface Flatness (P-V):	λ/10 @ 10.6μm	Surface Quality:	40-20
Wavelength Range (nm):	750 - 14000		
Material Properties			
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):		12.6	
Density (g/cm ³):		4.43	

Technical Information



Products

Dia. (mm)	Thickness (mm)	Coating	Model Number	Stock Number	Price	Buy
#16-796 Clearance						
						
Clearance						
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.						
25.40	1.00	Uncoated	AM-W-25-1		€562,38	3 In Stock
#16-797 Clearance						
						
Clearance						
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.						
25.40	3.00	Uncoated	AM-W-25-3		€682,89	5 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com