

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 0.36X 1/2" Gold TL™ Telecentric Lens



#58-257 (0.36X)

Stock #58-257 3-4 DAYS



1



€2.035,00

ADD TO CART

Qty 1+

€2.035,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
150.00

Horizontal Field of View, 1/2" Sensor:
17.8mm

Filter Thread:
M58 x0.75 (Female)

Maximum Diameter (mm):
65.00

Weight (kg):

0.82
Numerical Aperture NA, Object Side: 0.03
Stock No. of Mounting Clamp: #56-025 Sold Separately
Resolution, Image Space MTF @ f/10: >70% @ 40 lp/mm
Number of Elements (Groups): 10 (7)
Note: GoldTL™
Horizontal Field of View, 1/1.8" Sensor: 20mm
Typical Telecentricity @ 588nm (°): <0.025
Typical Distortion @ 588nm (%): 0.100
Type: Telecentric Lens
Primary Magnification PMAG: 0.36X
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 117 - 142
Mount: C-Mount
Aperture (f/#): f/6 - f/18
Coating: λ/4 MgF ₂
Depth of Field (mm): ±3.7 at f/10 (20% @20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 20.0 x 15.0
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View