

[See all 36 Products in Family](#)

## 0.1 - 4.0 OD, 75 x 75mm, Kodak Wratten 2 Neutral Density Filter Kit (13 Filters)



Stock #15-115 [CONTACT US](#)

− 1 + €2.740<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€2.740,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Filters Included :**  
Optical Densities: [0.1](#), [0.2](#), [0.3](#), [0.4](#), [0.5](#), [0.6](#), [0.7](#), [0.8](#), [0.9](#), [1.0](#), [2.0](#), [3.0](#), [4.0](#)

**Type:**  
Neutral Density Filter

**Number of Filters:**  
13

### Physical & Mechanical Properties

**Dimensions (mm):**

75 x 75 (Nominal)

75.00

Length (mm):

75.00

Width (mm):

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Available in Large Sizes
- Easily Cut for Custom Sizing
- Kodak Filter No. 96

Kodak Wratten 2 Neutral Density Filters are used in image forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. These ND filters feature tolerances of  $\pm 10\%$  of the nominal diffuse density. Although the filters transmit the infrared spectrum, neutrality is controlled only in the visible spectrum. Kodak Wratten 2 Neutral Density Filters are uncoated and have a blocking wavelength range of 400-700nm. All ND filters are 0.1mm in thickness and can be cut for easy custom sizing.

**Note:** Storage in humid environments can cause the filters to cloud and temperatures should not exceed 50°C for extended periods. Every 0.3 density increment equals one f-stop.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools