

[See all 153 Products in Family](#)

# 0.1 OD, 12.5mm Dia., VIS 0° Coated, Absorptive ND Filter

See More by [Hoya](#)



Anti-Reflection (AR) Coated HOYA Absorptive Neutral Density (ND) Filters

Stock **#13-078** 20+ In Stock

-

1

+

€63<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €63,00 each                   |
| Qty 11-25      | €55,00 each                   |
| Qty 26-49      | €52,50 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Neutral Density Filter

Stock No. of Uncoated Filter:

#63-456

Physical & Mechanical Properties

|           |                             |
|-----------|-----------------------------|
| 12.50     | Diameter (mm):              |
| 1.20 ±0.5 | Thickness (mm):             |
| ±0.1      | Dimensional Tolerance (mm): |
| <0.02     | Parallelism (mm):           |

Optical Properties

|                                          |                                              |
|------------------------------------------|----------------------------------------------|
| 0.1 ± 0.03 @ 400-700nm (Uncoated Filter) | Optical Density OD (Average):                |
| 0.08 @ 550nm                             | Nominal Optical Density @ Center of Coating: |
| Hoya ND70                                | Glass/Filter Number:                         |
| ND Filter Glass                          | Substrate: <div></div>                       |
| VIS 0° (425-675nm)                       | Coating:                                     |
| 1.50                                     | Index of Refraction (n <sub>d</sub> ):       |
| 80-50                                    | Surface Quality:                             |
| 79.0 (average) @ 400 - 700nm             | Transmission (%):                            |
| 400 - 700                                | Blocking Wavelength Range (nm):              |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm     | Coating Specification:                       |
| 425 - 675                                | Wavelength Range (nm):                       |

Material Properties

|     |                                  |
|-----|----------------------------------|
| 470 | Transformation Temperature (°C): |
|-----|----------------------------------|

Regulatory Compliance


|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 250:                  |


## Product Details

- Optical Densities from 0.1 to 4.0
- VIS 0°, NIR I, and NIR II Coating Options
- 12.5, 25, and 50mm Diameter Sizes
- Uncoated [HOYA](#) or [SCHOTT](#) ND Filters Also Available

Anti-Reflection (AR) Coated HOYAAbsorptive Neutral Density (ND) Filters feature HOYA colored glass substrates that are AR coated on both surfaces to reduce back reflections in the visible or near-infrared (NIR) spectra. VIS 0°, NIR I, and NIR II broadband AR coatings cover the spectral ranges of 425-675nm, 600-1050nm, and 750-1550nm. These neutral density filters attenuate light via absorption and can be stacked together to achieve custom optical densities to meet application requirements. Anti-Reflection (AR) Coated HOYAAbsorptive Neutral Density (ND) Filters are ideal for use in imaging and detection applications to reduce stray light, as well as in general filter stacking applications to control intensity. The standard metric diameters of 12.5, 25, and 50mm are compatible with our [TECHSPEC® C, S, and T-Mount Circular Optic Mounts](#) for benchtop applications.

## Technical Information





## Coating Curves

### Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts