

[See all 76 Products in Family](#)

LightPath 354125 | 11mm Dia., 0.50 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#33-425** **20+ In Stock**

[Other Coating Options](#)

-

1

+

€119^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	€119,00 each
Qty 11-49	€107,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads


General	
Thickness: 0.25 (t) (mm) Material: B-K7	Compatible Window:
354125	Lightpath Lens Code:
Aspheric Lens	Type:

Typical Applications:	
Collimate or Focus Laser Light	
Physical & Mechanical Properties	
Diameter (mm):	11.00 ±0.015
Clear Aperture CA (mm):	10
Edge Thickness ET (mm):	1.092
Center Thickness CT (mm):	3.64 ±0.40
Bevel:	Protective as needed
Optical Properties	
Effective Focal Length EFL (mm):	10.00 @ 633nm
Numerical Aperture NA:	0.5
Substrate: ☐	D-ZK3
Focal Length Tolerance (%):	±1
Aspheric Design Wavelength (nm):	633
Coating:	BBAR (350-700nm)
Coating Specification:	R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality:	60-40
f/#:	1.00
Wavelength Range (nm):	350 - 700
Working Distance (mm):	7.8
Conjugate Distance:	Infinite
Transmitted Wavefront Error (λ, RMS):	< 0.09
Environmental & Durability Factors	
Operating Temperature (°C):	≤200
Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 247:	Compliant

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



;